## HITEMP140-TSK HITEMP140 DATA LOGGER WITH THERMAL SHIELD

# TipTemp.com

#### Features

- Withstands Temperatures between -200°C up to 250°C
- Small Diameter 2.0" (51mm)
- Submersible
- Immediate or Delay Start
- Up to 1 Second Reading Rate

#### **Benefits**

- Validate a Wide Range of Temperature Processes Using One Data Logger
- HiTemp140 can be used With or Without Thermal Shield
- **Durable Thermal Shield Protects Probe** and Allows for a Fast Response Time

#### **Applications**

- **Peanut Roasting**
- **Food Processing**
- Meat Processing
- **Autoclave Validation**
- Conveyer Ovens
- Dishwasher Testing
- Incubator Validation

The HiTemp140-TSK is a kit that includes a HiTemp140 data logger housed in a thermal shield. The combined features of the  $\pm 0.1\%$ accuracy of the HiTemp140 and the properties of the durable thermal shield allow the device to be used for a wide range of validation applications. This rugged system can be placed in and withstand temperature from -200°C to 250°C, making it ideal for use in autoclave validation, monitoring food processing and dishwasher testing.




Flush

Using the MadgeTech software, the data logger is fast and easy to setup. Remove the thermal shield and place the HiTemp140 into the IFC400 docking station (sold separately). Using the software, an immediate or delay start can be chosen, as well as the reading rate. Select Start to program the settings and start the data logger. Place the thermal shield around the HiTemp140 and screw it back together. The device is ready to be deployed.

The HiTemp140-TSK can be completely submerged and is built for applications that require extreme temperature monitoring.

#### MADGETECH DATA LOGGER SOFTWARE



## **Software Features:**

- Multiple graph overlay
- **Statistics**
- Digital calibration
- Zoom in/zoom out
- Lethality equations (F<sub>0</sub>, PU)
- Mean Kinetic Temperature
- Full time zone support
- Data annotation
- Min./Max./Average lines
- Data table view
- Automatic report generation
- Summary view
- Multilingual

340 W. Broad St. Burlington, NJ 08016 USA Phone (609) 239-1900

## **HITEMP140 SPECIFICATIONS (DATA LOGGER)\***

Probe Measurement Range: -200°C to +260°C (-328°F to +500°F)

Temperature Resolution: 0.01°C (0.02°F)
Calibrated Accuracy: ±0.1°C/±0.18°F

(20°C to +140°C/68°F to +284°F)

±0.3°C/±0.54°F

(-20°C to +19.99°C/-4°F to +67.98°F)

±0.4°C/±0.72°F

(-40°C to -20.01°C/-40°F to -4.02°F)

Start Modes: Software programmable immediate start

Delay start up to 18 months in advance

Stop Modes: Manual or Timed (specific date and time)

Real Time Recording: May be used with PC to monitor and record

data in real time

Password Protection: An optional password may be programmed into

the device to restrict access to configuration options. Data may be read out without the password.

Memory: 32,700 readings

Wrap Around: Yes

Reading Rate: 1 second up to once every 24 hours

Battery Type: 3.6V high-temperature lithium battery included;

user replaceable

Battery Life: 1 year typical (1 minute reading rate at 25°C/77°F)

Calibration: Digital calibration through software

Calibration Date: Automatically recorded within device

Data Format: Date and time stamped °C, °F, K, °R

Time Accuracy: ±1 minute/month at 20°C to 30°C (68°F to 86°F)

Computer IFC400 docking station required; 125,000 baud

Interface:

Software: XP SP3/Vista/Windows 7/Windows 8

Operating -40°C to +140°C (-40°F to +284°F),

Environment: 0%RH to 100%RH

Dimensions (Body): 1.9" x 0.970" dia. (48mm x 24.6mm dia.)

Model Number: Dimensions (Probe)

HITEMP140-2 2.0" x 0.188" dia. (51mm x 4.8mm dia.) HITEMP140-2-TD 2.0" x 0.125" dia. (0.188" transitional dia.) 51mm x 3.2mm dia. (4.8mm transitional dia.)

HITEMP40-5.25 5.25" x 0.188" dia. (133mm x 4.8mm dia.) HITEMP140-5.25-TD 5.25" x 0.125" dia. (0.188" transitional dia.) 133mm x 3.2mm dia. (4.8mm transitional dia.)

HITEMP140-7 7.0" x 0.188" dia. (178mm x 4.8mm dia.)

Weight: 4.2 oz (120g)

Material: 316 Stainless Steel

Approvals: CE

#### HITEMP140-TSK SPECIFICATIONS\*

Operating -200 to +250°C (-328 to +482°F)
Environment: (Time limited)
0 to 100% RH

Dimensions: Flush Top: 2.75" x 2.0"dia.

(69.85mm x 51mm dia.) Vented Top: 4.3" x 2.0"dia. (109.2mm x 50.8mm dia.)

Material: Enclosure: PTFE

Weight: Flush Top: 8.2 oz. (232.5g) (not including data logger) Vented Top: 9.9 oz. (280.7g) (not including data logger)

BATTERY WARNING: WARNING: FIRE, EXPLOSION, AND SEVERE BURN HAZARD. DO NOT SHORT CIRCUIT, CHARGE, FORCE OVER DISCHARGE, CRUSH, PENETRATE, OR INCINERATE. BATTERY MAY LEAK OR EXPLODE IF HEATED ABOVE 150°C (302°F).

\*SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE. SPECIFIC WARRANTY

REMEDY LIMITATIONS APPLY. CALL 1-603-456-2011 OR GO TO WWW.MADGETECH.COM FOR DETAILS.

\*\*Other probe lengths up to 7" available. Contact MadgeTech for details.

Ambient Temperature	Exposure Time in Air	Exposure Time in Liquid	
-200°C (-328°F)	18 minutes	N/A	
-180°C (-292°F)	19 minutes	N/A	
-160°C (-256°F)	21 minutes	N/A	
-140°C (-220°F)	24 minutes	N/A	
-120°C (-184°F)	27 minutes	N/A	
-100°C (-148°F)	32 minutes	N/A	
-80°C(-112°F)	40 minutes	N/A	
-60°C (-76°F)	55 minutes	25 minutes	
-40°C (-40°F)	70 minutes	32 minutes	
-20°C to +140°C (-4°F to +284°F)	Indefinitely	Indefinitely	
150°C (302°F)	88 minutes	40 minutes	
160°C (320°F)	75 minutes	34 minutes	
170°C (338°F)	63 minutes	29 minutes	
180°C (356°F)	55 minutes	26 minutes	
190°C (374°F)	50 minutes	23 minutes	
200°C (392°F)	45 minutes	21 minutes	
210°C (410°F)	42 minutes	19 minutes	
220°C (428°F)	39 minutes	18 minutes	
230°C (446°F)	36 minutes	17 minutes	
240°C (464°F)	34 minutes	16 minutes	
250°C (482°F)	32 minutes	15 minutes	

### ORDERING INFORMATION

MODEL	DESCRIPTION	PRICE (U.S.)	Enclosure
HITEMP140-2-TSK	HiTemp-2-140 data logger and thermal shield	\$549.00	Flush or Vented
HITEMP140-5-TSK	HiTemp-5-140 data logger and thermal shield	\$549.00	Flush or Vented
HITEMP140-7-TSK	HiTemp-7-140 data logger and thermal shield	\$549.00	Flush or Vented
IFC400	Docking station with USB cable, software and manual	\$120.00	
ER1425S-HT	Replacement battery for the HiTemp140-PT	\$50.00	
NIST	NIST Calibration Certificate	\$60.00	

Humidity ASK ABOUT Pressure **OUR OTHER** DATA Level Shock **LOGGERS** LCD Display Pulse/Event/State Current Voltage Wireless Intrinsically Safe Spectral Vibration Motion

Temperature

\*To order the product with the NIST certificate add -CERT to the end of the part number and add \$60.00 to the price.